


## BL-OTG - Round spacers with metric thread



### Details:

- **Material: POM**
- **Colour: natural**
- Materials available on special order: Nylon, white PTFE
- Working temperature: -30°C to +110°C

| Symbol       | Int. thread<br>d | Ext. diameter<br>D | Int. thread length<br>P1 = P2 | Height<br>L | Material | Color   |
|--------------|------------------|--------------------|-------------------------------|-------------|----------|---------|
|              |                  | [mm]               | [mm]                          | [mm]        |          |         |
| BL-OTG-M3-05 | M3               | 6                  | 5                             | 5           | POM      | natural |
| BL-OTG-M3-06 | M3               | 6                  | 6                             | 6           | POM      | natural |
| BL-OTG-M3-08 | M3               | 6                  | 8                             | 8           | POM      | natural |
| BL-OTG-M3-10 | M3               | 6                  | 10                            | 10          | POM      | natural |
| BL-OTG-M3-12 | M3               | 6                  | 12                            | 12          | POM      | natural |
| BL-OTG-M3-15 | M3               | 6                  | 15                            | 15          | POM      | natural |
| BL-OTG-M3-18 | M3               | 6                  | 18                            | 18          | POM      | natural |
| BL-OTG-M3-20 | M3               | 6                  | 20                            | 20          | POM      | natural |
| BL-OTG-M3-25 | M3               | 6                  | 10                            | 25          | POM      | natural |
| BL-OTG-M3-30 | M3               | 6                  | 10                            | 30          | POM      | natural |
| BL-OTG-M3-35 | M3               | 6                  | 10                            | 35          | POM      | natural |
| BL-OTG-M3-40 | M3               | 6                  | 10                            | 40          | POM      | natural |
| BL-OTG-M3-45 | M3               | 6                  | 10                            | 45          | POM      | natural |
| BL-OTG-M3-50 | M3               | 6                  | 10                            | 50          | POM      | natural |
| BL-OTG-M3-55 | M3               | 6                  | 10                            | 55          | POM      | natural |
| BL-OTG-M3-60 | M3               | 6                  | 10                            | 60          | POM      | natural |
| BL-OTG-M4-05 | M4               | 8                  | 5                             | 5           | POM      | natural |
| BL-OTG-M4-06 | M4               | 8                  | 6                             | 6           | POM      | natural |
| BL-OTG-M4-08 | M4               | 8                  | 8                             | 8           | POM      | natural |
| BL-OTG-M4-10 | M4               | 8                  | 10                            | 10          | POM      | natural |
| BL-OTG-M4-12 | M4               | 8                  | 12                            | 12          | POM      | natural |
| BL-OTG-M4-15 | M4               | 8                  | 15                            | 15          | POM      | natural |
| BL-OTG-M4-18 | M4               | 8                  | 18                            | 18          | POM      | natural |

| Symbol       | Int. thread<br>d | Ext. diameter<br>D | Int. thread length<br>P1 = P2 | Height<br>L | Material | Color   |
|--------------|------------------|--------------------|-------------------------------|-------------|----------|---------|
|              |                  | [mm]               | [mm]                          | [mm]        |          |         |
| BL-OTG-M4-20 | M4               | 8                  | 20                            | 20          | POM      | natural |
| BL-OTG-M4-25 | M4               | 8                  | 10                            | 25          | POM      | natural |
| BL-OTG-M4-30 | M4               | 8                  | 10                            | 30          | POM      | natural |
| BL-OTG-M4-35 | M4               | 8                  | 10                            | 35          | POM      | natural |
| BL-OTG-M4-40 | M4               | 8                  | 10                            | 40          | POM      | natural |
| BL-OTG-M4-45 | M4               | 8                  | 10                            | 45          | POM      | natural |
| BL-OTG-M4-50 | M4               | 8                  | 10                            | 50          | POM      | natural |
| BL-OTG-M4-55 | M4               | 8                  | 10                            | 55          | POM      | natural |
| BL-OTG-M4-60 | M4               | 8                  | 10                            | 60          | POM      | natural |
| BL-OTG-M5-05 | M5               | 10                 | 5                             | 5           | POM      | natural |
| BL-OTG-M5-06 | M5               | 10                 | 6                             | 6           | POM      | natural |
| BL-OTG-M5-08 | M5               | 10                 | 8                             | 8           | POM      | natural |
| BL-OTG-M5-10 | M5               | 10                 | 10                            | 10          | POM      | natural |
| BL-OTG-M5-12 | M5               | 10                 | 12                            | 12          | POM      | natural |
| BL-OTG-M5-15 | M5               | 10                 | 15                            | 15          | POM      | natural |
| BL-OTG-M5-18 | M5               | 10                 | 18                            | 18          | POM      | natural |
| BL-OTG-M5-20 | M5               | 10                 | 20                            | 20          | POM      | natural |
| BL-OTG-M5-25 | M5               | 10                 | 10                            | 25          | POM      | natural |
| BL-OTG-M5-30 | M5               | 10                 | 10                            | 30          | POM      | natural |
| BL-OTG-M5-35 | M5               | 10                 | 10                            | 35          | POM      | natural |
| BL-OTG-M5-40 | M5               | 10                 | 10                            | 40          | POM      | natural |
| BL-OTG-M5-45 | M5               | 10                 | 10                            | 45          | POM      | natural |
| BL-OTG-M5-50 | M5               | 10                 | 10                            | 50          | POM      | natural |
| BL-OTG-M5-55 | M5               | 10                 | 10                            | 55          | POM      | natural |
| BL-OTG-M5-60 | M5               | 10                 | 10                            | 60          | POM      | natural |