


BL-OTG - Round spacers with metric thread



Details:

- **Material: POM**
- **Colour: natural**
- Materials available on special order: Nylon, white PTFE
- Working temperature: -30°C to +110°C

Symbol	Int. thread d	Ext. diameter D	Int. thread length P1 = P2	Height L [mm]	Material	Color
		[mm]	[mm]			
BL-OTG-M3-05	M3	6	5	5	POM	natural
BL-OTG-M3-06	M3	6	6	6	POM	natural
BL-OTG-M3-08	M3	6	8	8	POM	natural
BL-OTG-M3-10	M3	6	10	10	POM	natural
BL-OTG-M3-12	M3	6	12	12	POM	natural
BL-OTG-M3-15	M3	6	15	15	POM	natural
BL-OTG-M3-18	M3	6	18	18	POM	natural
BL-OTG-M3-20	M3	6	20	20	POM	natural
BL-OTG-M3-25	M3	6	10	25	POM	natural
BL-OTG-M3-30	M3	6	10	30	POM	natural
BL-OTG-M3-35	M3	6	10	35	POM	natural
BL-OTG-M3-40	M3	6	10	40	POM	natural
BL-OTG-M3-45	M3	6	10	45	POM	natural
BL-OTG-M3-50	M3	6	10	50	POM	natural
BL-OTG-M3-55	M3	6	10	55	POM	natural
BL-OTG-M3-60	M3	6	10	60	POM	natural
BL-OTG-M4-05	M4	8	5	5	POM	natural
BL-OTG-M4-06	M4	8	6	6	POM	natural
BL-OTG-M4-08	M4	8	8	8	POM	natural
BL-OTG-M4-10	M4	8	10	10	POM	natural
BL-OTG-M4-12	M4	8	12	12	POM	natural
BL-OTG-M4-15	M4	8	15	15	POM	natural
BL-OTG-M4-18	M4	8	18	18	POM	natural

Symbol	Int. thread d	Ext. diameter D	Int. thread length P1 = P2	Height L [mm]	Material	Color
		[mm]	[mm]			
BL-OTG-M4-20	M4	8	20	20	POM	natural
BL-OTG-M4-25	M4	8	10	25	POM	natural
BL-OTG-M4-30	M4	8	10	30	POM	natural
BL-OTG-M4-35	M4	8	10	35	POM	natural
BL-OTG-M4-40	M4	8	10	40	POM	natural
BL-OTG-M4-45	M4	8	10	45	POM	natural
BL-OTG-M4-50	M4	8	10	50	POM	natural
BL-OTG-M4-55	M4	8	10	55	POM	natural
BL-OTG-M4-60	M4	8	10	60	POM	natural
BL-OTG-M5-05	M5	10	5	5	POM	natural
BL-OTG-M5-06	M5	10	6	6	POM	natural
BL-OTG-M5-08	M5	10	8	8	POM	natural
BL-OTG-M5-10	M5	10	10	10	POM	natural
BL-OTG-M5-12	M5	10	12	12	POM	natural
BL-OTG-M5-15	M5	10	15	15	POM	natural
BL-OTG-M5-18	M5	10	18	18	POM	natural
BL-OTG-M5-20	M5	10	20	20	POM	natural
BL-OTG-M5-25	M5	10	10	25	POM	natural
BL-OTG-M5-30	M5	10	10	30	POM	natural
BL-OTG-M5-35	M5	10	10	35	POM	natural
BL-OTG-M5-40	M5	10	10	40	POM	natural
BL-OTG-M5-45	M5	10	10	45	POM	natural
BL-OTG-M5-50	M5	10	10	50	POM	natural
BL-OTG-M5-55	M5	10	10	55	POM	natural
BL-OTG-M5-60	M5	10	10	60	POM	natural